

Morse

suspension lamp



Table of contents

1. Product overview	Page 2
2. Finishes and materials	Page 2
3. Light Source & dimming	Page 2
4. Photometric data and technical information	Page 2
5. Functionality & accessories	Page 3
6. Recommended use & installation height	Page 3
7. Installation	Page 3
8. Ordering codes	Page 4
9. Certifications & standards	Page 5
10. Maintenance & Cleaning	Page 5

Versions



MOR_3915
Page 4

Morse

suspension lamp

1. Product overview

Metallic suspension lamp with integrated LED, providing direct lighting. Equipped with three independent heads, each rotatable up to 320°, allowing precise light direction towards the table, wall, or ceiling. Height adjustable.

Multiple Morse units can be mechanically linked using a connector piece (Union Kit) to extend the installation length. Each unit requires its own ceiling-mounted electrical connection.



2. Finishes and Materials



Surface Canopy: 26 Black

Body: 26 Black

Recessed Canopy: 26 Black
74 White

3. Light Source & Dimming

Lamping per head

LED 6,2W (2700K / Ang. 60° / >90 CRI / 350mA) 230V / Typ* 725 lumens

*Integrated LED module (included).

Dimming options:

Standard: TRIAC


Optional: DALI, CASAMBI

Optional optic lens: embedded aluminium optic lens 30°.

4. Photometric Data and Technical Information

Photometric data corresponds to the output of each individual lamp. Access to photometric files in download area.

2D / 3D / BIM Files available. Access to files in download area here.



Morse

suspension lamp

5. Functionality & Accessories

Rotating heads



Lens





Standard: Acrylic optic lens 60°.
Diffused light.

Accessory: 3 units of embedded optic lens 30°.
Focused direct light.
Code: 123530263

Possible compositions

Accessory: Union KIT for
more than one MORSE
Code: 123915002



6. Recommended use & Installation height

Suitable for general lighting, as well as for direct illumination above dining tables, countertops, bars, or desks. We **recommend positioning** the light source approximately **85 cm above the surface**. For more accurate information, refer to the photometric report.

7. Installation

Surface canopy



Recessed canopy with remote driver



Ø 55 mm drill on
dropped ceiling

Morse

suspension lamp

8. Ordering Codes

Lamping

LED 3x6,2W (2700K / Ang. 60° / >90 CRI / 350mA)
230V / Typ* 3x725 lumens

DIM: TRIAC (Optional DALI, CASAMBI)

Finishes

Surface Canopy:
26 Black
74 White

Body:
26 Black



Drawing	Mounting	Finish Canopy	Finish Body	Ordering Code
<p>MOR_3915S</p>	Surface mounted. Driver in the canopy.	Black White	Black Black	MOR_3915S_2626W MOR_3915S_7426W
<p>MOR_3915R</p>	Recessed, Remote driver Ø 50 mm drill	Black	Black	MOR_3915R_2626W

Lens Ordering Codes:

Black


3 units of 123530263

One 30° embedded lens per head

Morse

suspension lamp

9. Certifications & Standards



Warranty: 2 years

100% made in Spain

10. Maintenance & Cleaning

Our lighting fixtures are crafted with high-quality materials and finishes to ensure durability and timeless elegance. To maintain their original beauty, please follow these care recommendations:

1. Regular cleaning: Dust the fixture regularly using a soft, dry microfiber cloth to prevent buildup.
2. For deeper cleaning: If necessary, use a slightly damp cloth with clean water. Always dry the surface immediately with a dry cloth.
3. Avoid harsh products: Do not use alcohol, abrasive cleaners, solvents, or detergents, as they may damage the finish and alter the appearance.

In case of failure, LEDs can be easily replaced.